

## Datasheet

ENGLISH

# 1000W Fixed Installation DC-AC Power Inverter Modified sine, 24V dc / 230V ac

Stock number: 816-0062

RoHS 



### Specifications:

Model	816-0062
Rated power	1000W
Surge power	2000W
Output voltage	230V
Output frequency	50Hz $\pm$ 3
Output waveform	Modified sine wave
USB port	5V 2.1A
Input voltage	24V
Dimension(LxWxH)	270.4x208x77mm
N.W/unit	2480g

### Features:

- Anodized aluminum case provides durability & max heat dissipation
- Two LED indicators on the front panel shows the working and failure state
- ON/OFF switch control the inverter by hand
- The inverter is compact, light weight and east to operate.
- Protections: overheat, overload, low-voltage alarm & shutdown, over-voltage, short circuit, reverse polarity
- Soft start
- Auto. Reset after being in protected
- Universal UK/Euro output socket:

