

WHEEL FS 80X30/40 PB SWL FORK M22

Wheel series FS

High temperatures wheels (270°C / 518°F) in a thermoplastic compound with plain bore. For manual applications. Excellent shock resistance with minimal rolling resistance. Load rating according to EN12527 & EN12532, without obstacles. When present, do not apply brake at temperatures > 40°C (104°F).
 Plain bore wheel.




Castor series M22

M22 series, Medium-light pressed steel fork assemblies; swivel version has double ball raceways. Zincplated.

Technical data

| | | |
|----------------------------|-----|-----------|
| Wheel diameter | D | 80 mm |
| Tyre width | E | 30,0 mm |
| Bore diameter | d | 12 mm |
| Weight article | | 0,580 kg |
| Hub width | L | 40 mm |
| Overall height | H | 106 mm |
| Top plate outer dimensions | AxB | 102x83 mm |
| Bolt hole spacing | axb | 76x55 mm |
| Bolt hole spacing | axb | 80x60 mm |
| Fixing bolt diameter | g | M8 |
| Offset | F | 33 mm |
| Fork width | U | 40 mm |
| Load Capacity | | 120 kg |



Related Articles

Spare part wheel: [28002](#)

Version with trailing brake: [28702FR](#)

GENERAL INFORMATION / RECOMMENDATIONS AND WARNINGS

The cited text and the complete catalogue in their most up-dated versions are available in the OEM's website page www.lagspa.it/downloads. The dimensions, descriptions, specifications and illustrations herein are indicative and subject to variations without notice. The fact that products are illustrated herein does not necessarily imply they are available from stock nor does it place us under any obligation to supply them. Tests carried out refer to the original products with original accessories: the replacement of one of the components with others of different manufacture might prevent the same results from being achieved and will automatically invalidate any guarantee. Please contact our technical service concerning any special application.