



DEWALT 18V XR Cordless 16G Straight Nailer – Bare Unit

DCN662N-XJ



- 18V XR Brushless 16Ga nailer offers the cutting edge in nailing technology
- Brushless motor offers runtime that cannot be beaten in a compact package
- Compact, lightweight and ergonomic design makes the tool easy and comfortable to use but durable enough for worksite environment
- Mechanical rather than gas operation offers low running costs and consistent performance at low temperatures
- Sequential mode allows for precision placement and the bump operating mode provides the user with production speed of up to 4 nails per second
- Depth of drive can be easily adjusted using the thumb wheel depth adjuster
- Tool free stall / jam clearance minimises down time
- Trigger and contact trip lock-off and prevent accidental discharge of fastener

Description:

The DEWALT 18V XR Brushless 16G Straight Fix Nailer is a powerful heavy duty yet ultra-compact tool designed for delivering consistent drive quality, accuracy and extensive runtime. The brushless motor offers increased efficiency and power delivery, resulting in less wear and greater tool life. The straight magazine design and micro nose tip ensures accurate positioning of the fastener for all round straight fixing. The tool free stall and jam release help minimise downtime. The depth of drive can be adjusted tool free using the integrated thumb wheel. The nailer is ideal for applications such as installation of skirting boards, door and window trim, panelling, cabinetry, crown and cap and shoe moulding.

What we like – Two modes for precision and accurate or faster application speeds up to 4 nails per second for improved efficiency and reliability.

Comes with – Cordless nailer.

Specifications	
Power	18 V
Battery Capacity	5.0 Ah
Cells	6 x 2.5Ah cells
Nose Type	Micro Nose
Nail Lengths	32-64 mm
Nail Diameter	16Ga / 1.6mm
Magazine	Straight