

1-77-319



- It has a working range of 30m (spot) / 10m (line)
- It projects 5 beams (3 horizontal, 1 vertical, 1 plumb) and 1 horizontal line >120°
- Improved accuracy spec
- Out of true level sensor
- It has a magnetically dampened pendulum
- The special base allows magnet to steel rails + pivoting
- The pendulum has a locking device for safe transportation
- Runs on 3 AA batteries