


Cartridge QSP14-5/16-U

Part number: 172986

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Mounting position	optional
Design	Straight design
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 60 °C
Type of mounting	Mounting pin
Pneumatic connection, port 1	Cartridge 14 mm
Pneumatic connection, port 2	For tubing outside diameter of 5/16"
Ambient temperature	23 °F ... 140 °F
Colour of release ring	grey
Note on materials	RoHS-compliant
Material housing	Nickel-plated
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel