

PICCOLO ABS C 85 G



Sample photo

Order symbol: ABS C 85 G
Product nbr: 8784306
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002099
El. number:
 Finland: 3423457
 Electric No. 8212001860
 Denmark:
 Electric No. Italy: 7211025
 Electric No. Sweden: 2536711

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	140	80	85	CHM-3	DIN-35 Mounting rail
inch:	5.5	3.1	3.3	FP 22040	Wall fastening lug (2 pcs)

Materials:	Rating:
Material: ABS	Ingress Protection (EN 60529): IP66/IP67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	Flammability Rating: UL 94 HB
Gasket material: Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4X, 6, 12, 13

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Accessories:	
C-MP	Mounting plate

