



Main

Range of product	OptiLine 45
Cabling installation system	Post
Product type	Post
Type of post	One-sided
Pole/post surface finish	Anodized

Complementary

Colour	Natural
Fixing mode	Screw-fixed
Front opening size	45 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	430 mm
Width	68 mm
Market segment	Small commercial Residential

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN-AW-6063 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP30

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations