

FEATURES

- Slim line size for discreet install
- Energy saving, highly efficient LED's
- Driver on board technology
- Swivel mounting bracket for range of positions

RS PRO 10W REX Slim Floodlight

RS Stock No.: 2175272



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- 10W LED floodlighting solution
- Suitable for a number of residential applications – such as garages, driveways and gardens
- High quality aluminium casing offers a durable fitting
- IP65 rating for total protection against dust and low-pressure jets of water

General Specifications

Length	104mm
Width	27mm
Height	92mm
Weight	0.23kg
Colour Temperature	4000K

Mechanical Specifications

Construction Materials	Aluminium body & Toughened glass
Cable Length	0.5m
Replaceable Lamp	No
Dimmable	No
Beam Angle	110°

Electrical Specifications

Operating Wattage	10W
Operating Voltage	AC 220-240V 50/60Hz
Power Factor	≥0.9
Lumens	900 Lm
Luminous Efficiency	90Lm/W
CRI	≥70

Protection Category

IK Rating	IK06
IP Rating	IP65
Lifespan	30,000Hrs

Additional Information

EAN	5016211419444
Custom Tariff Number	94054010

Approvals

Declarations	CE Declaration of Conformity
Standards Met	BS EN 60598-1

Similar Products

Stock No.	Brand	Product Name	Colour Temperature	Lumens	IP Rating
217-5273	RS PRO	20W REX Slim Flood	4000K	1800LM	IP65
217-5275	RS PRO	30W REX Slim Flood	4000K	2700Lm	IP65

