

A50.20.063 -10...+50°C L1=160x9mm copper alloy CL.2

Bimetallic thermometer TYP48-50

Item number:	14026083	
Quantity:	1 pcs.	
Order code:	A50.20.063-H-CAB-160DMFRGD-1ZZZZZZZQK-ZZZ	2BZTM5003
Overview:	A50.20.063 -10...+50°C L1=160x9mm copper alloy CL.2 Case material: steel, zinc plated Pointer: aluminium, black Window: acrylic, (SAN) detachable, with retainer screw; Mat.=Cu-alloy G1/2B Dial background: white *WIKA* Data sheet: TM50.03	
Details:	Bimetallic thermometer TYP48-50 Model: A50 Standard version Design: standard, steel case Nominal size [NG, d1]: 63 mm Case material: steel, zinc plated Unit: °C Scale range: -10 °C ... +50 °C Insertion length L1: 160 mm Stem diameter: 9 mm Stem material: copper alloy Thermowell: detachable, with retainer screw; Thermowell material: Cu-alloy Process connection: G 1/2 B Manufacturer logo: *WIKA* Pointer: aluminium, black Window: acrylic, (SAN) Accuracy class: class 2 per EN 13190 Dial background: White Data sheet: TM50.03	