

Features

- **Flexible Locking Positions** – Allows valve handle to be locked in fully closed, partially open, or fully open positions for complete control.
- **Durable ABS Construction** – Made from **high-strength ABS**, offering resistance to chemicals, cracking, and abrasion.
- **Adjustable Fit** – Fits valve stems up to **35 mm diameter**, ensuring compatibility with a wide range of butterfly valves.
- **Secure Padlock Locking Provision** – For multiple users, a **hasp** can be added.
- **Weather & Chemical Resistant** – Built to **withstand extreme temperatures and harsh environments**, suitable for both indoor and outdoor use.
- **Simple Two-Part Design** – Easy to install with the main body and end cap that jams the valve handle in the set position.

Product Description

RS PRO Adjustable Lockout for Stainless Steel Butterfly Valve with Pull Handle

RS Stock No.: 0694365



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *Designed to effectively secure pull-handle butterfly valves commonly used in industries such as food and beverage, water utilities, chemical, pharmaceutical and wherever stainless-steel pipes are used for liquids.*
- *The lockout device allows you to secure the valve handle in any desired position, whether completely closed, partially open, or completely open, providing flexibility and control over the valve operation.*
- *The lockout device consists of a long main body and end cap. These two pieces are easily installed on the valve body cap & handle rod, jamming the lever in the desired position and preventing any movement.*
- *Freely adjustable, fits most stainless-steel pull-handle butterfly valve lock handle lengths.*
- *The lockout device features holes that allow the installation of 1 padlock at a precise position. For installing more padlocks use a hasp.*
- *Constructed from strong ABS; resistant to cracking, abrasion, and various chemicals, ensuring its durability and longevity in demanding industrial environments.*
- *Can withstand extreme weather conditions and temperature fluctuations, making it suitable for both indoor and outdoor use.*
- *Temperature resistance -20 °C to 90 °C*
- *The lockout device fits over the valve stem up to a diameter of 35mm.*
- *Completely adjustable to fit a range of valve handles, the cover slides to fit over the end of the valve where it can be locked in place.*
The standard colour is Red

General Specifications

Type	Butterfly Valve Lockout
Material	ABS
Colour	Red
Padlock holes	22
Package	PE-LD

Mechanical Specifications

Accept padlock shackle up to	6.5mm
Fits stem up to (Diameter)	35mm
Weight	76 Grams

Operation Environment Specifications

Withstand temperature	-20 °C to 90 °C
------------------------------	-----------------