



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:43 (UTC)



23128CKE4

Spherical Roller Bearings

Boundary Dimensions

d	140	mm	Bore diameter
D	225	mm	Outside diameter
B	68	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	725000	N	Basic dynamic load rating
C0r	945000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	2400	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3200	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1200	min-1	Grease lubrication
Oil (Oil-bath)	1600	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	152	mm	Diameter of shaft abutment
da (max.)	158	mm	Diameter of shaft abutment
Da (min.)	198	mm	Diameter of housing abutment
Da (max.)	213	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.28	Constant
Y2	3.6	Axial load Factors
Y3	2.4	Axial load Factors
Y0	2.3	Axial load Factors

Mass

Mass approx.	10.5	kg	Mass approx.
--------------	------	----	--------------

Associated products

Adapter	H3128	Adapter
Withdrawal sleeve	AHX3128	Withdrawal sleeve

