



29161025

1610 - Taper bushes

2D Technical Drawing

Dynamic 3D View
Technical Specifications

TYPE (TYPE)	1610
Ø D1 (D1) mm	57
Part number (CODE)	29161025
Design (EXEC)	A
L (L) mm	25
Ø D2 H8 only prebore (D2S)	-
Ø D2 with ISO G7 hole, DIN 6885-JS9 slot (D2CF)	25
keyway width (B) mm	8
keyway depth (T2) mm	3.3
British Standard Whitworth (SCREWS)	3/8"x5/8"
Tightening torque (TT) N/m	19.6
Weight (WEIGHT) kg	0.35
Material (MAT)	Gray cast iron