

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

Similar figure

Product description

Mobile handheld device, battery-powered, for processing on-tape ferrules 1.5 mm² with functional end, suitable for PVC insulated conductors (H07V-K), CUTFOX 12 cable cutter, waste guide plate 2, service tool for error correction, and one strip of ferrules 1.5 mm², packed in a robust case.

Your advantages

- Consistently optimum results thanks to automatic monitoring functions
- Unlimited mobile use thanks to battery operation and magazine
- The product innovation for switchgear manufacturing: the Crimphandy. You can strip and crimp your conductors in under two seconds using this portable handheld device. This represents a time saving of 75%.

Commercial data

Item number	1212466
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH3
Product key	BH3233
GTIN	4046356589154
Weight per piece (including packing)	1,883 g
Weight per piece (excluding packing)	1,463 g
Customs tariff number	84672920
Country of origin	DE

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

Set consists of

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device

1212466

<https://www.phoenixcontact.com/in/products/1212466>



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

CF CRIMPHANDY 1,5/SERVICE-TOOL - Assembly tool

1212708

<https://www.phoenixcontact.com/in/products/1212708>



Service tool, for CF-CRIMPHANDY 1,5, for rectifying malfunctions

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

CF CRIMPHANDY 1,5/GP2 - Replacement part

1212844

<https://www.phoenixcontact.com/in/products/1212844>

Waste guide plate 2, for CF CRIMPHANDY 1,5



CUTFOX 12 - Cable-cutting tool

1212128

<https://www.phoenixcontact.com/in/products/1212128>

Cable cutter, for copper and aluminum up to 12 mm diameter (up to 35 mm²)



CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

Technical data

Product properties

Product type	Automatic crimping device
Compression	Square crimp
Conductor type	PVC H07V-K
Insertion length minimum	32 mm
Product property	Portable automatic stripping and crimping device
	Integrated magazine
	Capacitive sensor
	Rechargeable lithium-ion battery
	Capacitive sensor

Electrical properties

Frequency range	60 Hz
Power consumption	20 W

Supply

Supply voltage range	7.4 V DC
----------------------	----------

Connection data

Conductor connection

Cross section range, metric	1.5 mm ² ... 1.5 mm ²
Stripping length	10.8 mm

Dimensions

Width	43 mm
Height	70 mm
Length	205 mm
Conductor diameter range	2.4 mm ... 3.1 mm

Material specifications

Color	black
-------	-------

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 10.0	EC002778
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF CRIMPHANDY 1,5 - Automatic stripping and crimping device



1212466

<https://www.phoenixcontact.com/in/products/1212466>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in