



## GBC 240HS Home Office A3 Laminator

The GBC 240HS is a sleek and efficient solution for everyday laminating needs. Designed with both style and performance in mind, this high-speed A3 laminator is ideal for home or home office use. Boost productivity and reduce lamination time by 30% using GBC high-speed pouches. With a fast 2-minute warm-up time, it laminates a 75-micron A4 sheet in just 45 seconds, making it perfect for efficiently handling your home projects. The easy-to-use control switch offers three pouch thickness settings from 75-125 microns, providing flexibility for various document types. An anti-jam release lever ensures smooth operation by effortlessly resolving any misfed pouches. Additionally, the smart status LED system simplifies operation with clear visual and audible cues: red during warm-up, blue with a sound when ready, and an automatic shut-off after 15 minutes of inactivity to conserve energy. Protect and preserve your important documents with a perfect finish, every time. Black and red colour.



### Attributes

- Fast warm-up time, ready to use in just 2 minutes.
- Compatible with pouches from 75 to 125 microns. Laminates ID card up to A3 sized documents.
- GBC High-Speed laminators reduce lamination time by 30% when using GBC high-speed pouches.
- Laminates an A4 document (75 mic) in just 45 seconds.
- Laminates 13 x A4 in 10 minutes.
- SMART status LED: glows red during warm-up and turns blue with an acoustic signal when the laminator is ready to use.
- The jam release lever allows easy manual removal of misfed or jammed pouches.
- Includes a starter pack of 5x A4 pouches (75 microns).
- Conserve energy with the 15-minute auto shut-off feature, which activates after detecting inactivity.
- Low noise level <50Dba for less distractions.
- For best results use with GBC document pouches.
- CE certified, TUV/GS.

### Specifications

Number	4410069UK
Colour	Black/Red
Material	ABS Plastic
Dimensions (W x H x D)	460 x 87 x 151 mm
Laminating Speed (mm/min)	400
Temperature	123C-135C
Power Supply	220-240V AC 50/60Hz
Warm up Time (min)	2
Heating System	2 from outside heated rollers
Operation Mode	2 roller, no carrier, temperature controlled
Max. Laminating Width (mm)	330
Max. Laminating Thickness (mm)	0.5
Max. Pouch Thickness (microns)	75-125
Power Consumption (W)	550
Dimensions (with Tray) mm	460 x 87 x 151
Anti-Jam Technology	Manual release lever
Approx. lamination time (A4)	45 secs (A4 80 micron)
Photo friendly	Yes
Period of Warranty (Years)	2
Type	Pouch
Weight	2200 g
Pallet quantity	0
EAN code	5028252645546