

Zarges GRP Teletower

The Proud Winner of 2011's Innovation Award at the Executive Hire Show

The Teletower is one of the most exciting and innovative products to be developed for the access industry in years! Its unique patented telescopic operation means it is easy to transport, store and erect; the Teletower offers an efficient and lower-cost alternative to other low level access platforms. Providing 4 metres of working height, from van to insitu in 3 minutes or less!

- Telescopic Mechanism allows 5 Adjustable Platform Heights from 1.00m to 2.00m (Working Heights from 3.00m to 4.00m)
- Operates as a podium with low level fixed height options of 33cms and 61cms
- Fully erected in under 3 minutes saving down time and man hours
- Can be transported in a small van or estate car
- Comprises only two parts – Tower and Platform (no more leaving parts in the yard)
- GRP (non conductive)
- Large Folding Aluminium Work Platform (1.40m x 0.70m) with climb through hatch
- Integral Telescopic hand and knee rails
- Integral Platform Stabilisers
- Integral Stabilising Legs with 5 Optional Positions
- Lockable castors
- Single Person Operation
- Minimal Product footprint for ease of Transportation and Storage
- Optional Toe - Boards
- Conforms to EN1004

Product code	Includes pack of 4 toe boards	Material / version	Platform height options (m)	Max. working height (m)	Max. height incl. railing (m)	Weight (kg)
TT005 RS: 7990648	Yes	Fibreglass	0.33 / 0.61 / 1.00 / 1.25 / 1.50 / 1.75 / 2.00	4.00	2.95	61



Closed



Open to 2metres