sub-base **VABS-S4-1S-G14-K2** Part number: 539725

FESTO

with port pattern according to standard 15407/-2.



Data sheet

Feature	Value
Width	26 mm
Based on the standard	ISO 15407-2
Assembly position	Any
Pilot air supply	external
Operating pressure	-0.9 10 bar
Operating voltage range AC	110 V
Operating voltage range DC	24 V
Surge strength	4 kV
Acceptable current load at 40°C	2 A
Degree of contamination	3
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP65
	NEMA 4
	in assembled condition
Ambient temperature	-5 50 °C
Product weight	302 g
Mounting type	with through hole
	according to ISO 15407-2
Materials note	Conforms to RoHS
Material of connecting plate	Aluminium die cast