HyFlex®

ADVANCED MECHANICAL PROTECTION

11-616

The reference for tactility, dexterity and flexibility

Multi Purpose | Light Duty

Ultra-thin PU-coated gloves, boasting high tactility and dexterity, for delicate handling

- **Enhanced dexterity:** HyFlex® 11-616 industrial gloves' light 18-gauge liner reduces strain and simplifies repetitive motion
- **Optimized tactility:** Their ultra-thin polyurethane coating optimizes tactile sensitivity and grants them a "second skin" feel, perfect for delicate handling
- **Improved durability:** The same PU coating helps these HyFlex® gloves satisfy ANSI/EN abrasion resistance standards
- **Considered aesthetics:** HyFlex® 11-616 industrial working gloves' dark nylon liner hides dirt and stains, extending glove life
- **Certified skin-friendliness:** Dermatest® certification ensures skin-friendly hand protection



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Construction
- Transportation
- Logistics
- Warehousing

Applications

- Picking, fastening components
- Assembling and mounting components
- Fastening components, parts

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-616

The reference for tactility, dexterity and flexibility

Key Features

- Light 18-gauge design: Highly dexterous safety gloves
- Ultra-thin polyurethane coating: For a tactile, "second skin" effect
- Dark nylon liner: Durable PPE gloves that hide dirt and stains

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant

CE ANSI 3 ABR ANSI A1 CUT ORIGINAL 10 EXCELLENT 2019 dermatest dermatest-guarantee.de SILVER 2022 ecovadis Sustainability Rating EN388: 2016 2121X

Specifications

BRAND | STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-616	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	195-245 mm	Black	• 12 pairs/bag; 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region
Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia
Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region
Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II.
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada
Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell