

## 53CSA High Precision Swiss Tweezers



- Crush-proof design, smooth action
- Very fine points

| Cat No. | UPC No.      | Packed | Length |     | Dimension "A" |     | Dimension "C" |     | Shelf Pack |
|---------|--------------|--------|--------|-----|---------------|-----|---------------|-----|------------|
|         |              |        | Inch   | mm  | Inch          | mm  | Inch          | mm  |            |
| 53CSA   | 043127608599 | Sleeve | 4.25   | 108 | .335          | 8.5 | .015          | 0.4 | 1          |

## 65ASA High Precision Swiss Tweezers

Erem



- Fine, bent tips
- For extra fine chips and miniature components
- Tips angled at 150°

| Cat No. | UPC No.      | Packed | Length |     | Shelf Pack |
|---------|--------------|--------|--------|-----|------------|
|         |              |        | Inch   | mm  |            |
| 65ASA   | 043127608865 | Sleeve | 5.5    | 140 | 1          |

## 249SA High Precision Swiss Tweezers



- Synthetic heat resistant tips to 480° F (250° C)
- Waterproof
- Acid resistant
- Resistant to molten solder (for brief periods)
- ESD safe

| Cat No. | UPC No.      | Packed | Length |     | Shelf Pack  |
|---------|--------------|--------|--------|-----|-------------|
|         |              |        | Inch   | mm  |             |
| 249SA   | 043127066528 | Sleeve | 5.00   | 127 | 1           |
|         |              |        |        |     | RS 176-1172 |

## 258SA High Precision Swiss Tweezers



- Very fine, synthetic heat resistant tips to 480° F (250° C)
- Acid resistant
- Waterproof
- Resistant to molten solder
- ESD safe

| Cat No. | UPC No.      | Packed | Length |     | Shelf Pack  |
|---------|--------------|--------|--------|-----|-------------|
|         |              |        | Inch   | mm  |             |
| 258SA   | 043127629037 | Sleeve | 4.75   | 121 | 1           |
|         |              |        |        |     | RS 176-1188 |