

900MC/TX

Socket drivers for Torx® head screws, coloured, 1/4" female drive, chrome-plated - burnished inserts



	art.	Ø	Ø mm	L mm	L1 mm
009002721	900MC/TX 10	T10	12	28	12
009002722	900MC/TX 15	T15	12	28	12
009002723	900MC/TX 20	T20	12	28	12
009002724	900MC/TX 25	T25	12	28	12
009002725	900MC/TX 27	T27	12	28	12
009002726	900MC/TX 30	T30	12	28	12
009002727	900MC/TX 40	T40	12	28	12



Ø	
T10	Green
T15	Dark Green
T20	Grey
T25	Purple
T27	Red
T30	Orange
T40	Blue

