

PRODUCT-DETAILS

OS630B12P

OS630B12P SWITCH FUSE



General Information

Extended Product Type	OS630B12P
Product ID	1SCA022825R6400
EAN	6417019283807
Catalog Description	OS630B12P SWITCH FUSE
Long Description	Switch Fuses,Front Operated,3-pole,12 (Between the Poles),British Standard,C1-C2,Handle and shaft included,

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country of Origin	Finland (FI)

Popular Downloads

Data Sheet, Technical Information	1SCC311013C0201
Instructions and Manuals	1SCC311016M0210

Dimensions

Product Net Width	341 mm
-------------------	--------

Product Net Height	306 mm
Product Net Depth / Length	233 mm
Product Net Weight	13.5 kg

Technical

Rated Operational Current AC-21A (I_e)	(500 V) 630 A (690 V) 630 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 630 A (500 V) 630 A (690 V) 630 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 630 A (500 V) 630 A (690 V) 630 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 200 kW (400 V) 355 kW (415 V) 355 kW (500 V) 450 kW (690 V) 630 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 630 A
Conventional Thermal Current (I_{the})	Fully Enclosed 570 A
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	Main Circuit 690 V AC
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 18 kiloampere rms
Rated Conditional Short-Circuit Current (I_{nc})	(690 V) 80 kA
Power Loss	at Rated Operating Conditions per Pole 60 W
Pollution Degree	3
Handle Type	Pistol handle and shaft included 12 (Between the Poles)
Position of Line Terminals	Top In - Bottom Out, Bottom In - Top Out
Fuse Size	C1-C2
Fuse System	British Standard
Operating Mode	Front Operated
Standards	IEC 60947-3
Mounting Type	Base mounting
Number of Poles	3
Terminal Type	Lug terminals
Terminal Width	39 mm
Tightening Torque	50 ... 75 N·m
Rated Current (I_n)	Main Circuit 630 A

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
-------------	--

Certificates and Declarations (Document Number)

CCC Certificate	CCC OS630-800 2016
-----------------	--------------------

Declaration of Conformity - CE	1SCC311112D2704
DNV GL Certificate	1SCC311131D0202
EAC Certificate	EAC OT_OTDC_OTL_OTP_OTR_OTU_OTE_OETL_OESA_OESC_OTM_OS_OSM_p f
Instructions and Manuals	1SCC311016M0210
RoHS Information	1SCC311112D2704

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	328 mm
Package Level 1 Depth / Length	365 mm
Package Level 1 Height	260 mm
Package Level 1 Gross Weight	13.5 kg
Package Level 1 EAN	6417019283807

Classifications

Object Classification Code	Q
ETIM 4	EC001040 - Fuse switch disconnecter
ETIM 5	EC001040 - Fuse switch disconnecter
ETIM 6	EC001040 - Fuse switch disconnecter
ETIM 7	EC001040 - Fuse switch disconnecter
ETIM 8	EC001040 - Fuse switch disconnecter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Fuses

