

Eaton 160NHG02B-400

Catalog Number: 160NHG02B-400

Fuse-link, LV, 160 A, AC 400 V, NH02, gL/gG, IEC, dual indicator, live gripping lugs

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	160NHG02B-400
	EAN
	5027590437325
Product Length/Depth	Product Height
150 mm	63 mm
Product Width	Product Weight
40 mm	427 g
Compliances	Certifications
RoHS Compliant	IEC 60269-1
CE Marked	IEC 60269-2
	DIN 43620



Product specifications

Type

Fuse

Application

industrial

Utilities, Solar, Wind

Amperage Rating

160 A

Fitted with:

Metal gripping lugs

Fuse size

NH02

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

400 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Resources

Catalogs

NH Fuse links, bases and gear

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[CA134002EN](#)

Declarations of conformity

[UKCA NH Size 02/2, 400V fuse-links](#)

[CE NH Size 02/2, 400V fuse-links](#)

Multimedia

[Eaton Bussmann – NH fuse link portfolio](#)

Presentations

[NH Overview Video](#)

Technical data sheets

[720099 NH 400 Volts gG](#)

Technical service bulletins

[Datasheet - 160NHG02B-400](#)

Watt losses

10 W

Connection

Blade end

Construction

NH02

Construction size

NH02

Fuse shape

Square body

Knife blade contacts

Voltage type

AC

Suitable for

Microswitch BVL50

Material

Ceramic body

Quantity

3

Voltage rating

400 V

Rated switching capacity AC

120 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia