



## VM-4HDT

1:4 4K60 4:2:0 HDMI to Long-Reach  
HDBaseT DA

| HDMI | HDCP Compliant | HDBaseT  
| 4K/60 UHD (4:2:0)



VM-4HDT is a high-quality, long-reach 4K@60Hz (4:2:0) HDBaseT extender distributor that takes one HDMI input, with IR and RS-232 control signals, converts them to HDBaseT extension line signal and distributes it to four HDBaseT outputs that connect to compatible HDBaseT receivers

## FEATURES

**High Performance Distribution** - Distributes one HDMI signal to four long-reach HDBaseT extension outputs with up to 4K video resolution

**Extension-line Distribution** - Distributes a 4K@60Hz (4:2:0) 24bpp (maximum) video signal over HDBaseT extension line to a distance of up to 40m (130ft) long-reach, and even further for lower video resolutions

**Standard Compatibility** - Connects to any HDBaseT compliant extension product on the market

**HDMI Signal Transmission** - HDCP 1.4 compliant signal, supporting Deep Color, x.v.Color™, Lip Sync, 7.1 PCM, Dolby TrueHD, DTS-HD, 2K, 4K, and 3D as specified in HDMI 2.0. EDID and CEC (OUT 1 only) signals are passed through from the source to the display

**I-EDIDPro™ Kramer Intelligent EDID Processing™** - An intelligent EDID handling, processing and pass-through algorithm that ensures Plug and Play operation for HDMI source and display systems

**Kramer Equalization & re-Klocking™ Technology** - Rebuilds the digital signal integrity to travel longer distances

**EDID Pass-through** - Pass-through algorithm ensures Plug and Play operation for HDMI source and display systems

**LED Indicators** - Status indicators for HDMI and HDBaseT input/output connected signals and power for ease of maintenance and troubleshooting

**Easy Installation** - Twisted-pair cables for HDBaseT signals wiring. Compact Mega TOOLS™ fan-less enclosure for over-ceiling mounting, or side-by-side rack mounting



## TECHNICAL SPECIFICATIONS

---

Inputs	1 HDMI On an HDMI female connector
Outputs	4 HDBT On RJ-45 female connectors
Ports	1 IR On a 3.5mm mini jack for IR link extension 1 RS-232 On a 3-pin terminal block for serial link extension
Video	Max. Data Rate 10.2Gbps (3.4Gbps per graphic channel) Max. Resolution 4K@60Hz (4:2:0) 24bpp Standards Compliance Supports HDCP 1.4 and HDBaseT 1.0 HDMI Support Deep Color, x.v.Color™, Lip Sync, 7.1 PCM, Dolby TrueHD, DTS-HD, 2K, 4K, and 3D as specified in HDMI 2.0
Extension Line	Up to 40m (130ft) At 4K@60Hz (4:2:0) Note: When using Kramer HDBaseT cables Up to 70m (230ft) At full HD (1080p @60Hz 36bpp) Note: When using Kramer HDBaseT cables
General	Controls EDID setup button, 12 setup DIP switches Indicator LEDs OUTPUTS 1-4, LINK 1-4, active input, power on 1 RS-232 On a Mini-USB female connector for firmware upgrade
Environmental Conditions	Operating Temperature 0° to +40°C (32° to 104°F) Storage Temperature -40° to +70°C (-40° to 158°F) Humidity 10% to 90%, RHL non-condensing
Power	Source 5.2V DC, 4A Consumption 5V DC, 800mA
Enclosure	Size MegaTool Type Aluminum Cooling Fan ventilation
Accessories	Included Power supply
Product Dimensions	18.75cm x 11.50cm x 2.54cm (7.38" x 4.53" x 1.00" ) W, D, H
Product Weight	0.5kg (1.2lbs) approx
Shipping Dimensions	34.50cm x 16.50cm x 5.20cm (13.58" x 6.50" x 2.05" ) W, D, H
Shipping Weight	1.3kg (2.8lbs) approx

