



DCS575T2

**54V XR FLEXVOLT 190mm Circular Saw
kitted 2x batteries**

Selling Proposition

- Scale for precise cutting depth setting to 67 mm
- General purpose ripping, cross-cutting and bevelling circular saw for wood and other construction materials
- High torque motor for durability and power for cutting job site and joinery materials
- Stable block construction for low vibration running and long service life
- Additional handle for safe two-handed work
- Variable adjustment of the bevel angle to 57 degrees

Standard Equipment

- Precision 24 tooth saw blade
- Rip Fence
- Blade Spanner
- T-STAK
- Dust Extraction Spout

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
No Load Speed	5800 rpm
Blade Diameter	190 mm
Blade Bore	30 mm
Bevel Capacity	57 °
Max. Depth of Cut at 90°	67 mm
Max. Depth of Cut at 45°	49 mm
Max. Depth of Cut at 45°[with guide rails]	NA mm
Weight	3.6 kg