BAHCO

## 90

# ERGO™ Central Nut Adjustable Wrenches with Rubber Handle and Phosphate Finish

## PRODUCT DETAILS

- Adjustable wrenches developed according to the scientific ERGO™ process
- Maximum comfort with minimum effort thanks to ergonomic design
- Jaw will not fall out even at maximum opening of the wrench
- Head combines slim design for accessibility with strength for performance
- Laser scale in mm for pre-adjusting and accurate measurement
- Skydrol- and oil-resistant rubber handle
- Ergonomically designed thermoplastic elastomer handle distributes pressure uniformly in the hand, reducing the risk for work related injuries
- High-performance alloy steel forged in single piece
- Phosphate finish, precision-hardened and anti-corrosion treated
- Left turning screw
- Standards: ISO 6787, DIN 3117, ASME B107.8 and BS 6333




**Follow the Fish!**

PRODUCT ATTRIBUTES

| Product | A | A | B | C | D | E | g |
|---|---|---|---|---|---|---|---|
| 9070 | 158 mm | 6 in | 20 mm | 5.3 mm | 11.3 mm | 19 mm | 139 g |
| 9071 | 208 mm | 8 in | 27 mm | 6 mm | 12.9 mm | 24 mm | 272 g |
| 9072 | 257 mm | 10 in | 31 mm | 8.7 mm | 15.5 mm | 29 mm | 425 g |
| 9073 | 308 mm | 12 in | 34 mm | 11.9 mm | 17.6 mm | 34 mm | 730 g |