

Datenblatt

Power USB Built-In Socket

Art. Nr. 67331000 (BP)

Art. Nr. 67331500 (SP)

06.04.2016

Input Voltage:	8 - 34 Volt
Output Voltage:	5 Volt
Output current max.:	3 A
Current consumption:	< 5 mA (open circuit operation)
Overload protection:	yes
Protection against overheating:	yes
Reverse voltage protection:	yes
Connections:	cable end 6 mm tin coated
Panel thickness:	2 mm up to 16 mm
Installation inner diameter:	27,8 mm

Material:

Housing:	ABS
Temperature stress:	max. 110 °C

Cable:

Strand:	2 x 0,5 mm ² red/black
Length:	150 mm

Power USB Built-In Socket

Art. Nr. 67331000 (BP)

Art. Nr. 67331500 (SP)

06.04.2016

