

## FEATURES

- Plan Shank
- Various lengths
- HSS for performance and safety
- Perfect for general workshop and maintenance use

## RS PRO HSS Twist Drill Bit, 0.5mm x 22mm

RS Stock No.: 787-7337



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Brought to you by RS PRO, a range of jobber drill bits suitable for high-speed metal, wood and plastic drilling. Designed as a twisted drill bit, these attachments guarantee excellent performance and will be an asset to your application. All models are highly reliable and excellent quality.

### General Specifications

<b>Drill Bit Type</b>	Twist Drill Bit
<b>Type</b>	Twist
<b>Material</b>	70% flute length is made of HSS
<b>Surface</b>	Black Finish
<b>Shank Type</b>	Reduced
<b>Drilling Application</b>	Construction, electrical or masonry applications

### Mechanical Specifications

<b>Overall Length</b>	22mm
<b>Point Angle</b>	118°
<b>Diameter</b>	0.5mm
<b>Flute Length</b>	6mm

### Approvals

<b>Compliance/Certifications</b>	DIN338
----------------------------------	--------

RS Art.No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
7877315	0.25	19	3
7877327	0.30	19	3
7877324	0.35	19	4
7877330	0.40	20	5
7877321	0.45	20	5
7877337	0.50	22	6
7877333	0.55	24	7
7877349	0.60	24	7
7877346	0.65	26	8
7877352	0.70	28	9
7877343	0.75	28	9
7877359	0.80	30	10
7877355	0.85	30	10
7877361	0.90	32	11
7877368	0.95	32	11
7877365	1.05	34	12
7877374	1.10	36	14
7877377	1.25	38	16
7884984	1.65	43	20
7884987	1.75	46	22