

Datasheet

RS Pro GU10 LED Reflector Bulb 6 W(75W) 4200K, Cool White Non-Dimmable

RS Stock No: **786-9134**



Product Details

RS Pro GU10 LED reflector bulb in cool white colour, operates at a voltage rating of 220 to 240 V ac and power rating of 6 W. The bulb produces a brilliant white light with a colour temperature of 4200K. This non-dimmable bulb comes with an average life of 25,000 hours. It is ideal for applications in household luminaires, hotels, hospitals and office space.

Features and Benefits

- 5.5 W LED lamp as 75 W PAR16 replacement
- GU10 base
- 220-240 V ~ input voltage
- Non-dimmable
- Mercury free
- Average lifetime 25,000 hours

Specifications:

Beam Angle	40°
Colour Temperature	4000 K
Colour Tone	Cool White
Diameter	50 mm
Dimmable	No
EU Energy Efficiency Rating	A+
Incandescent Equivalent Wattage	75 W
Lamp Base	GU10
Length	55 mm
Life Hours	20000 h
Luminosity	220 lm
Retrofit	Integrated
Voltage Rating	220 to 240 V ac
Wattage	6 W

