

## Datasheet

### **RS Pro Terminal Strip, Straight, 12way, 2 Row, 15mm Fixing Centres, 76A, 400 V, length 175.5mm, Black**

RS Stock No: **703-3842**



## Product Details

RS Pro 12-way terminal block strip in black colour, has screw terminal for easy installation. It has 12 contacts that supports 16 mm<sup>2</sup> wire size. This terminal block is current rated for 76 A and voltage rating of 400 V. It comes in two rows with 15 mm pitch. This straight terminal measures 175.5 x 25.3 x 23 mm.

## Features and Benefits

- 12-way terminal blocks
- Black colour
- Screw termination
- Available in 24, 32, 57 and 76A



ENGLISH

### Specifications:

Body Orientation	Straight
Colour	Black
Current Rating	76 A
Depth	23 mm
Dimensions	175.5 x 25.3 x 23 mm
Fixing Centre	15 mm
Length	175.5 mm
Material	PP
Maximum Operating Temperature	+80°C
Number of Contacts	12
Number of Rows	2
Pitch	15 mm
Voltage Rating	400 V
Width	25.3 mm
Wire Size	16 mm <sup>2</sup>
Standards Met	BS EN 60998; CE Certified