

# STANLEY

FMHT70443-0

## STANLEY® FATMAX® 2-in-1 Multi Tacker

The STANLEY® FATMAX® 2-in-1 Multi Tacker is ideal for fastening in a range of professional applications such as stapling membrane to timber studs, polythene sheeting over fiberglass insulation, securing bead into pine skirting - plus fixing paper and card. It features a high and low power setting to control the intensity of the staple application, as well as a staple window which provides clear visibility of when a staple reload is required. Takes Type-A Staples and Type-J Brad Pins.



### FEATURES & BENEFITS

**EASY SQUEEZE TECHNOLOGY:** For reduced fatigue and added driving power into materials.

**ANTI-JAM MECHANISM:** Prevents fasteners jamming, for continuous use and reliable operation.

**HIGH-LOW POWER SETTING:** Controls intensity of staple application when working on a variety of hard and soft materials.

**STAPLE WINDOW:** Provides clear visibility to determine when staple reload is required.

**STAPLE RELOAD:** Easy to reload staple gun.

**INTEGRATED HANDLE LOCK:** For safe storage and transportation.

**SOFT GRIP HANDLE:** For added comfort.

**ALUMINIUM CONSTRUCTION:** For long-lasting durability.

**COMPATIBLE FASTENINGS:** Fires STANLEY® Tupe-A staples in 6mm - 14mm and STANLEY® Type-J Headed Brad Pins in 12mm - 15mm.

**STAPLES NOT INCLUDED.**



# STANLEY

## FEATURES & BENEFITS



### SUITABLE FOR A VARIETY OF APPLICATIONS

Ideal for stapling membrane to timber studs, polythene sheeting over fiberglass insulation, securing bead into pine skirting - plus fixing paper and card, and more.



### HIGH-LOW POWER SETTING

Controls intensity of staple application when working on a variety of hard and soft materials.



### STAPLE WINDOW

Provides clear visibility to determine when staple reload is required.



### STAPLE RELOAD

Easy to reload staple gun.



### SOFT GRIP HANDLE

For added comfort.



### COMPATIBLE FASTENINGS

Fires STANLEY® Tupe-A staples in 6mm - 14mm and STANLEY® Type-J Headed Brad Pins in 12mm - 15mm.