



## CarryLite LMS Location Management System



**CA-inserts** 

The CarryLite LMS (Location Management System) is a storage system comprising boxes with accessories, shelving units and trolleys for storage of several boxes. The system is versatile, lightweight and robust containing standard products as well as costumer specific solutions which are made to order.



CarryLite LMS

The CarryLite boxes were launched in 1996 and have proven to be a bestseller and probably the most versatile and robust storage box ever made. Naturally the CarryLite box became the cornerstone of the new Location Management System.



CarryLite LMS-FOD

Based on the insight and feedback raaco obtained from one of our long-time users of the CarryLite boxes (Airbus Group) we developed the new version called CarryLite LMS with a set of new features.



CarryLite with foam

The CarryLite LMS is a thought through system for organising workshops, assembly lines, maintenance & repair or similar workplaces, and is a highly usable system for everyone working with LEAN/5S principles.



CarryLite Depot

## CarryLite LMS


Location Management System



Depot for storage/organisation of several CarryLite boxes







raaco

## Major new features

#### Sandwich lid & Click'n grid

The double lid provides security and overview. It makes it possible to insert a description or layout of content, assembly instructions etc.

The Click'n grid ensures the inserts will remain in place once they are properly fixed in the bottom of the CarryLite box.





Sandwich document lid for description or layout of content, instructions etc.



Click'n grid feature to fix the insert in the box



Optional lower lid-part. U-profile to ensure smaller parts remain in place or smooth surface for better visibility of content



Fastener fixing holes for safety and security



Smooth surface for easy labelling/identification



RFID holder to hold RFID-Tag for tracking of box



Red dots – open/close identification



Colour ID-Tags for better identification purposes

## CarryLite boxes

The CarryLite LMS boxes come in two different sizes and in two different versions.

The two sizes are called 4x8 and 5x10 and share the same height. The two different versions are standard and FOD.

Both versions are made of high grade polypropylene and polycarbonate.







The CarryLite LMS comes in two sizes and in standard and FOD versions.



Sandwich document lid for description or instruction. U-profiles to ensure smaller parts remain in place.



Sandwich document lid for description or instruction. Smooth surface for better visibility.

## CarryLite LMS-FOD

The FOD versions of the CL-LMS range are manufactured in two special colours (RAL 2005 and RAL 2016) and with added fluorescent material for better visibility in dark surroundings.








## Inserts

The two different sizes of CarryLite LMS boxes can be configured to specific needs by use of 7 different sizes of inserts which ensures the content remains safe in the right location.


There are two different versions of the CA-inserts which look alike. Both are transparent but the FOD-version contains added fluorescent material for better visibility using black light (UV-light).

The range of CA-inserts can be fixed in the click'n grid at the bottom of the CarryLite LMS cases.









Click'n grid feature to fix the insert in the box.



U-profiles ensure smaller parts remain in place.

## Foam inlay

Organising tools in a foam inlay inside a CL-LMS box will not only protect the tools but also help in identifying missing tools before leaving the job.

raaco offers the opportunity to create customised foam inlay through an online web-enabled foam configurator.

Find more information on www.raaco.com





Have your own foam inlay specially made to fit your own tools.



## Trolley and Depot

#### **Location Management System**

Lightweight, robust, versatile and with excellent overview.


The CarryLite LMS System includes trolleys and depots for storage and organisation of several CarryLite boxes in one place.

raaco has 5 versions of trolleys and depots for different kinds of need for storage and organisation. raaco also offers the option of custom made trolleys and depots.

All trolleys and depots are made of lightweight aluminum.











Bearings with stops keep CarryLites in place during transportation



Magnet-lock holds the shelf in place when in collapsed position



Label holder for ID purposes



Two collapsible shelves to support 2 CarryLites in use



Two handles for easy manoeuvering



Four wheels with brakes ensure trolley remains in position, and strong bumpers (optional) to protect the surroundings

# Accessories and spare parts

Replaceable ID-tags in 8 different colours can be used for colour coding and labelling to ensure quick identification of the right CarryLite LMS box and content.

RFID holders for the two sizes of CL-LMS boxes can securely hold RFID labels/tags free of dust etc. The RFID holders are available in a standard as well as in a FOD version.

The CarryLite LMS system is designed for disassembly which makes it possible to replace a broken part in the rare case it is needed.





## CarryLite LMS product range >



#### CarryLite LMS 80 4x8-0/DLU R-BLU



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278

Colour: raaco blue Ot: 3

Item No.: 142540

#### CarryLite LMS 80 4x8-0/DL R-BLU



Compartment box with sandwich lid without U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278

Colour: raaco blue Ot: 3

Item No.: 142557

#### CarryLite LMS 80 4x8-0/DLU-FOD



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278 Colour: RAL 2005 / Fluorescent

Qt: 3

Item No.: 142564

#### CarryLite LMS 80 4x8-0/DL-FOD



Compartment box with sandwich lid without U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278 Colour: RAL 2005 / Fluorescent

Qt: 3

#### CarryLite LMS 80 4x8-0 R-BLU



Compartment box with sliding locks and handle, empty. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 81 x 337 x 278

Colour: raaco blue

Qt: 3

Item No.: 142885

#### CarryLite LMS 80 4x8-0/DLU-FOD-V2



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278 Colour: RAL 2016 / Fluorescent

Qt: 3

Item No.: 144865

#### CarryLite LMS 80 4x8-0/DL-FOD-V2



Compartment box with sandwich lid without U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 337 x 278 Colour: RAL 2016 / Fluorescent

Qt: 3

Item No.: 144872

#### Foam inlay (CarryLite 4x8)



You can have your own foam inlay specially made to fit your own tools. For protection during transport and to make it far easier to find your tools.

Produced to order (see page 23).

Fits into a CarryLite 4x8

Dim (HxWxD, mm): 83 x 333 x 273

Please contact raaco for more information at mail@raaco.com

#### CarryLite LMS 80 5x10-0/DLU R-BLU



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330

Colour: raaco blue Ot: 3

Item No.: 142502

#### CarryLite LMS 80 5x10-0/DL R-BLU



Compartment box with sandwich lid without U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330

Colour: raaco blue Ot: 3

Item No.: 142519

#### CarryLite LMS 80 5x10-0/DLU-FOD



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330 Colour: RAL 2005 / Fluorescent

Qt: 3

Item No.: 142526

#### CarryLite LMS 80 5x10-0/DL-FOD



Compartment box with sandwich lid without U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330 Colour: RAL 2005 / Fluorescent

Qt:3

#### CarryLite LMS 80 5x10-0 R-BLU



Compartment box with sliding locks and handle, empty. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 81 x 413 x 330

Colour: raaco blue

Qt: 3

Item No.: 142878

#### CarryLite LMS 80 5x10-0/DLU-FOD-V2



Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330 Colour: RAL 2016 / Fluorescent

Qt:3

Item No.: 144827

#### CarryLite LMS 80 5x10-0/DL-FOD-V2




Compartment box with sandwich lid and U-profiles, empty. The sandwich lid holds up to 5 sheets of paper of 80 mg. The box has a Click-bottom for attachment of CA-inserts, 2 RFID holders inside the box and fixing holes in the lid and the top of the base for sealing the box. Fitted with sliding locks and handle. Made of polypropylene (PP) with a strong polycarbonate (PC) lid.

Dim (HxWxD, mm): 83 x 413 x 330 Colour: RAL 2016 / Fluorescent

Qt: 3

Item No.: 144834

#### Foam inlay (CarryLite 5x10)



You can have your own foam inlay specially made to fit your own tools. For protection during transport and to make it far easier to find your tools.

Produced to order (see page 23).

Fits into a CarryLite 5x10

Dim (HxWxD, mm): 83 x 413 x 330

Please contact raaco for more information at mail@raaco.com

#### Insert 80 CA8-1



Insert 80 CA8-1 CLEAR in transparent or Insert 80 CA8-1 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 79 x 55

Colour: Transparent

Qt: 32

Item No.: 142892

Colour: Transp./Fluorescent

Ot: 32

Item No.: 142977

#### Insert 80 CA8-2



Insert 80 CA8-2 CLEAR in transparent or Insert 80 CA8-2 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 55 x 157

Colour: Transparent

5

Qt: 16

Item No.: 145015

Colour: Transp./Fluorescent

Qt: 16

Item No.: 145022

#### Insert 80 CA8-3



Insert 80 CA8-3 CLEAR in transparent or Insert 80 CA8-3 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 55 x 235

Colour: Transparent

Ot: 9

Item No.: 145039

Colour: Transp./Fluorescent

Qt: 9

Item No.: 145046

#### Insert 80 CA7-1



Insert 80 CA7-1 CLEAR in transparent or Insert 80 CA7-1 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 79 x 109

Colour: Transparent Colour: Transp./Fluorescent

Qt: 16

Item No.: 142984

Ot: 16

#### Insert 80 CA7-11/2



Insert 80 CA7-1½ CLEAR in transparent or Insert 80 CA7-1½ FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 79 x 163

Colour: Transparent Colour: Transp./Fluorescent

Qt: 8 Qt: 8

Item No.: 142915 Item No.: 142991

#### Insert 80 CA7-2



Insert 80 CA7-2 CLEAR in transparent or Insert 80 CA7-2 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 79 x 218

Colour: Transparent Colour: Transp./Fluorescent

Qt: 8 Qt: 8

Item No.: 144063 Item No.: 144087

#### Insert 80 CA6-1



Insert 80 CA6-1 CLEAR in transparent or Insert 80 CA6-1 FOD in transparent/fluorescent.

The insert has a click'n grid feature to fix the insert into the box. Can be used in all the CarryLite LMS compartment boxes.

Dim (HxWxD, mm): 69 x 157 x 109

Colour: Transparent Colour: Transp./Fluorescent

Qt: 8 Qt: 8

Item No.: 142922 Item No.: 143004

#### Depot/Trolley for CarryLite 4x8





Depot or trolley (empty) with space for 10 CarryLite 4x8 boxes. Both have bearings to keep the CarryLites in place and label holder for ID purposes.

The trolley has two handles, four wheels with brakes. Made of lightweight aluminium.

#### 4x8 Depot 10-0/1450

Dim (HxWxD, mm): 1450 x 415 x 425 Colour: Aluminium Qt: 1 Item No.: 144506

4x8 Trolley 10-0/1450

Dim (HxWxD, mm): 1580 x 415 x 425 Colour: Aluminium Qt: 1

Item No.: 144902

#### Depot/Trolley for CarryLite 5x10





Depot or trolley (empty) with space for 10 CarryLite 5x10 boxes. Both have bearings to keep the CarryLites in place and label holder for ID purposes.

The trolley has two handles, four wheels with brakes. Made of lightweight aluminium.

#### 5x10 Depot 10-0/1450

Dim (HxWxD, mm): 1450 x 490 x 480 Colour: Aluminium Qt: 1

Item No.: 141819

#### 5x10 Trolley 10-0/1450

Dim (HxWxD, mm): 1580 x 490 x 480 Colour: Aluminium Qt: 1

Item No.: 144896

#### CarryLite 80 5x10 Trolley CS/7-FOD



Trolley (empty) with space for 7 CarryLite 5x10 boxes. It has two collapsible shelves to support two CarryLites in use, a label holder for ID purposes, two handles, bearings with stop that keep the CarryLites in place, magnet-lock to hold the shelves in place, four wheels with brakes and strong bumpers to protect the surroundings. Made of lightweight aluminium.

5x10 Trolley CS/7-FOD

Dim (HxWxD, mm): 1280 x 550 x 530

Colour: Aluminium Qt: 1



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: raaco yellow Qt: 10

Item No.: 144315

#### CL-LMS ID-Tag R-GREY



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: raaco grey

Qt: 10

Item No.: 144322

# CL-LMS ID-Tag GREEN

Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Green Qt: 10

Item No.: 144339

#### **CL-LMS ID-Tag BLUE**



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Blue Qt: 10

Item No.: 144285

#### **CL-LMS ID-Tag RED**



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Red Qt: 10

Item No.: 144292

#### **CL-LMS ID-Tag ORANGE**



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Orange

Qt: 10

Item No.: 144308

#### **CL-LMS ID-Tag TURQUOISE**



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Turquoise Qt: 10

Item No.: 144346

#### CL-LMS ID-Tag BLACK



Dim (HxWxD, mm): 22 x 22 x 2,5

Colour: Black

Qt: 10

## CL-LMS RFID-Holder 4x8 FOD



Dim (HxWxD, mm): 42 x 83 x 8,6 Colour: Grey / Fluorescent

Qt: 1 (set)
Item No.: 284301

## CL-LMS RFID-Holder 5x10 FOD



Dim (HxWxD, mm): 42 x 114 x 8,6 Colour: Grey / Fluorescent

Qt: 1 (set)
Item No.: 284097

## CL-LMS RFID-Holder 4x8 R-Grey



Dim (HxWxD, mm): 42 x 83 x 8,6

Colour: raaco grey Qt: 1 (set) Item No.: 284875

#### CL-LMS RFID-Holder 5x10 R-Grey



Dim (HxWxD, mm): 42 x 114 x 8,6

Colour: raaco grey Qt: 1 (set)

Item No.: 284868

#### Foam (CarryLite 4x8)



Dim (HxWxD, mm): 83 x 333 x 273 Colour: Black

Produced to order (see page 23).

#### Foam (CarryLite 5x10)



Dim (HxWxD, mm): 83 x 413 x 330 Colour: Black

**Produced to order** (see page 23).

Item no.	Product	Dim. external (HxWxD, mm)	Dim. internal (HxWxD, mm)	Colour
CarryLite L	MS 4×8	(11,777,2), 11111)	(HXVVXD, HHII)	
142540	CL-LMS 80 4x8-0/DLU R-BLU	83 x 337 x 278	69 x 313 x 218	raaco blue
142557	CL-LMS 80 4x8-0/DL R-BLU	83 x 337 x 278	69 x 313 x 218	raaco blue
142564	CL-LMS 80 4x8-0/DLU-FOD	83 x 337 x 278	69 x 313 x 218	RAL 2005 / Fluorescent
142571	CL-LMS 80 4x8-0/DL-FOD	83 x 337 x 278	69 x 313 x 218	RAL 2005 / Fluorescent
142885	CL-LMS 80 4x8-0 R-BLU	81 x 337 x 278	69 x 313 x 218	raaco blue
144865	CL-LMS 80 4x8-0/DLU FOD-V2	83 x 337 x 278	69 x 313 x 218	RAL 2016 / Fluorescent
144872	CL-LMS 80 4x8-0/DL FOD-V2	83 x 337 x 278	69 x 313 x 218	RAL 2016 / Fluorescent
CarryLite LMS 5x10				
142502	CL-LMS 80 5x10-0/DLU R-BLU	83 x 413 x 330	69 x 392 x 272	raaco blue
142519	CL-LMS 80 5x10-0/DL R-BLU	83 x 413 x 330	69 x 392 x 272	raaco blue
142526	CL-LMS 80 5x10-0/DLU-FOD	83 x 413 x 330	69 x 392 x 272	RAL 2005 / Fluorescent
142533	CL-LMS 80 5x10-0/DL-FOD	83 x 413 x 330	69 x 392 x 272	RAL 2005 / Fluorescent
142878	CL-LMS 80 5x10-0 R-BLU	81 x 413 x 330	69 x 392 x 272	raaco blue
144827	CL-LMS 80 5x10-0/DLU FOD-V2	83 x 413 x 330	69 x 392 x 272	RAL 2016 / Fluorescent
144834	CL-LMS 80 5x10-0/DL FOD-V2	83 x 413 x 330	69 x 392 x 272	RAL 2016 / Fluorescent
CA-inserts - transparent				
142892	Insert 80 CA8-1 CLEAR	69 x 79 x 55	65 x 73 x 49	Transparent
145015	Insert 80 CA8-2 CLEAR**	69 x 55 x 157	65 x 51 x 153	Transparent
145039	Insert 80 CA8-3 CLEAR**	69 x 55 x 236	65 x 51 x 232	Transparent
142908	Insert 80 CA7-1 CLEAR	69 x 79 x 109	65 x 73 x 103	Transparent
142915	Insert 80 CA7-1 <sup>1</sup> /2 CLEAR	69 x 79 x 163	65 x 73 x 157	Transparent
144063	Insert 80 CA7-2 CLEAR	69 x 79 x 218	65 x 73 x 212	Transparent
142922	Insert 80 CA6-1 CLEAR	69 x 157 x 109	65 x 154 x 103	Transparent
CA-inserts - flourescent				
142977	Insert 80 CA8-1 FOD	69 x 79 x 55	65 x 73 x 49	Transparent / Fluorescent
145022	Insert 80 CA8-2 FOD**	69 x 55 x 157	65 x 51 x 153	Transparent / Fluorescent
145046	Insert 80 CA8-3 FOD**	69 x 55 x 236	65 x 51 x 232	Transparent / Fluorescent
142984	Insert 80 CA7-1 FOD	69 x 79 x 109	65 x 73 x 103	Transparent / Fluorescent
142991	Insert 80 CA7-1 <sup>1</sup> /2 FOD	69 x 79 x 163	65 x 73 x 157	Transparent / Fluorescent
144087	Insert 80 CA7-2 FOD	69 x 79 x 218	65 x 73 x 212	Transparent / Fluorescent
143004	Insert 80 CA6-1 FOD	69 x 157 x 109	65 x 154 x 103	Transparent / Fluorescent
Depots & Trolleys *				
142250	CarryLite 80 5x10 Trolley CS/7-0/1280	1280 x 550 x 530	_	Aluminum
144902	CarryLite 80 4x8 Trolley 10-0/1450	1580 x 415 x 425	_	Aluminum
144896	CarryLite 80 5x10 Trolley 10-0/1450	1580 x 490 x 480	_	Aluminum
144506	CarryLite 80 4x8 Depot 10-0/1450	1450 x 415 x 425	_	Aluminum
141819	CarryLite 80 5x10 Depot 10-0/1450	1450 x 490 x 480	_	Aluminum
ID-tags				
144315	CL-LMS ID-Tag R-YELLOW	22 x 22 x 2,5		raaco yellow
144322	CL-LMS ID-Tag R-GREY	22 x 22 x 2,5	_	raaco grey
144339	CL-LMS ID-Tag GREEN	22 x 22 x 2,5	_	Green
144285	CL-LMS ID-Tag BLUE	22 x 22 x 2,5	_	Blue
144292	CL-LMS ID-Tag RED	22 x 22 x 2,5	_	Red
144308	CL-LMS ID-Tag ORANGE	22 x 22 x 2,5	_	Orange
144346	CL-LMS ID-Tag TURQUOISE	22 x 22 x 2,5		Turquoise
144629	CL-LMS ID-Tag BLACK	22 x 22 x 2,5	_	Black
RFID-holde 284301	CL-LMS RFID-Holder 4x8 FOD	12 y 92 y 9 6	38 x 50 x 6	Grey / Flourescent
284097	CL-LMS RFID-Holder 4x8 FOD  CL-LMS RFID-Holder 5x10 FOD	42 x 83 x 8,6 42 x 114 x 8,6	38 x 59 x 6	Grey / Flourescent
284875	CL-LMS RFID-Holder 4x8 R-Grey	42 x 114 x 8,6 42 x 83 x 8,6	38 x 50 x 6	
284868	CL-LMS RFID-Holder 4x8 R-Grey  CL-LMS RFID-Holder 5x10 R-Grey	42 x 83 x 8,6 42 x 114 x 8,6	38 x 50 x 6	raaco grey
404000	CE-LIND WITH-LIGHTED DX IO K-CITES	46 X 114 X 0,0	D X EC X DC	raaco grey

DL = Double lid (sandwich lid)
DLU = Double lid with U-profiles

<sup>\*</sup> Made to order = any configuration made of standard parts. Leadtime 3 weeks.

Produced to order = any configuration made of non-standard parts. Lead time 8 weeks.

Please contact raaco for more information at mail@raaco.com

<sup>\*\*</sup> Available Q4.2017



raaco - supplier to Airbus since 1990

