

har-port 2x USB 2.0 A-A 1,0m cable



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1951
Specification	har-port 2x USB 2.0 A-A 1,0m cable
HARTING eCatalogue	https://harting.com/09454521951

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

Version

Cable length	1 m
Connection type	2x type A jack - type A connector
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	86.5 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140060692
eCl@ss	27060304 Appliance cord (data cable)
ETIM	EC002599
UNSPSC 24.0	43202222