

Cisco SFP-10G-BX-U-60 Compatible SFP+ Transceiver Module - 10GBase-BX (Upstream)

Product ID: SFP-10G-BX-U-60-ST



The SFP-10G-BX-U-60-ST is a Cisco SFP-10G-BX-U-60 compatible upstream fiber SFP+ transceiver which pairs with StarTech.com's SFP-10G-BX-D-60-ST. They are designed, programmed and tested to work with 10GBase-BX compatible Cisco switches and routers. The SFP+ transceiver module supports a maximum distance of up to 60 km (37.3 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- **Wavelength:** 1270nmTx/1330nmRx
- **Maximum Data Transfer Rate:** 10Gbps
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 60 km (37.3 mi)
- **Power Consumption:** Low power consumption
- **DDM:** Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- 100% Compatibility with Cisco SFP-10G-BX-U-60 guaranteed
- StarTech.com SFP+ modules are backed by a lifetime warranty
- Pairs with SFP-10G-BX-D-60-ST
- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption
- Hot-swappable with fiber-optic modules

	Warranty	Lifetime
Hardware	Compatible Brand	Cisco®
Performance	Power Consumption (In Watts)	< 1W
Physical Characteristics	Product Height	12.600
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	24.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000

Product appearance and specifications are subject to change without notice.