

| | |
|--------------------|--|
| Universe | Professional |
| Type | Verticality |
| Category | Harnesses |
| Subcategory | Harnesses for fall arrest, work positioning and suspension |



AVAO® SIT

The AVAO SIT work positioning and suspension seat harness is designed for greater comfort in all situations. Wide, semi-rigid waistbelt and leg loops give excellent support. Its lightweight, breathable construction maximizes air flow. The harness also facilitates the carrying and organizing of work tools, with multiple equipment loops and retainers for attaching CARITool tool holders and TOOLBAG tool-holder pouches. This seat harness is designed to be converted into a fall arrest harness when combined with a TOP chest harness, or into a rope access harness when combined with a TOP CROLL S or L chest harness. The AVAO SIT features leg loops with DoubleBack self-locking buckles.



Wide, semi-rigid waistbelt and leg loops give excellent support. Its lightweight, breathable construction maximizes air flow.




Waistbelt and leg loops equipped with self-locking DOUBLEBACK buckles allow quick and easy adjustment.

Short Description Comfortable seat harness for work positioning and suspension

- Selling Points**
- Comfortable throughout the workday: semi-rigid, wide waistbelt and leg loops for excellent support. Its lightweight, breathable construction maximizes air flow.
 - Practical adjustment:
 - waistbelt and leg loops equipped with self-locking DOUBLEBACK buckles for quick and easy adjustment
 - side attachment points can be folded down to prevent them snagging accidentally when not in use
 - Facilitates carrying and organization of tools:
 - six pre-shaped equipment loops with protective sheath
 - two slots for CARITool tool holder
 - four slots for TOOLBAG tool pouch

-
- Specification**
- Ventral attachment point: attachment for a descender or a positioning lanyard for use in single mode
 - Lateral attachment points: attachment for a positioning lanyard for use in double mode
 - Rear attachment point on the waistbelt: restraint lanyard attachment
 - Certification(s): CE EN 358, CE EN 813, EAC
 - Material(s): nylon, polyester, aluminum, steel
-

Specifications by reference

| Reference(s) | C079AA00 | C079AA01 | C079AA02 | C079AA03 |
|---------------|---|---|---|---|
| |  |  |  |  |
| Color(s) | black/yellow | black/yellow | black | black |
| Size | 1 | 2 | 1 | 2 |
| Waist belt | 70-93 cm | 83-120 cm | 70-93 cm | 83-120 cm |
| Leg loops | 47-62 cm | 50-65 cm | 47-62 cm | 50-65 cm |
| Weight | 1175 g | 1190 g | 1175 g | 1190 g |
| Made in | RO | RO | RO | RO |
| Guarantee | 3 years | 3 years | 3 years | 3 years |
| Packing | 1 | 1 | 1 | 1 |
| Case quantity | 6 | 5 | 6 | 5 |
| EAN | 3342540822481 | 3342540822498 | 3342540822504 | 3342540822511 |

Accessory(ies) CARITool
TOOLBAG

Related product(s) GRILLON HOOK European version
I'D@S