



OUR OFFER

Schneider Electric Time Delay Relays RE17 Series

Schneider Electric Time Delay Relays

RE17 Series

Stock No.	Schneider MPN	Function	Width	Supply Voltage	Timing Range
791-2711	RE17RAMU	On Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2708	RE17LAMW	On Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2727	RE17RHMU	On Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2705	RE17LHBM	On Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2745	RE17RMMU	Multi-function	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2749	RE17RMMW	Multi-function	17.5 mm	12-240 V ac	0.1 s- 100 h
791-2717	RE17LMBM	Multi-function	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2733	RE17RMEMU	Multi-function	17.5 mm	24-240 V ac	0.1 s- 10 h
791-2758	RE17RMXMU	Multi-function	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2742	RE17RMJU	Multi-function	17.5 mm	12 V ac/dc	0.1 s- 100 h
791-2723	RE17RCMU	Off Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2701	RE17LCBM	Off Delay	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2739	RE17RLMU	Asymmetrical	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2714	RE17LLBM	Asymmetrical	17.5 mm	24-240 V ac	0.1 s- 100 h
791-2736	RE17RLJU	Asymmetrical	17.5 mm	12 V ac/dc	0.1 s- 100 h
791-2720	RE17RBMU	One Shot	17.5 mm	24-240 V ac	0.1 s- 100 h



For more technical information please visit:

www.rs-online.com