



ENGLISH

Datasheet

RS 20 pairs , 100m CW1128 Telecom Cable Black Sheath

Stock Number - 520-2807



Description:

Rated Temperature (oC): -20 ~ 70

Rated Voltage (V):240

**Construction:****Conductor:** Bare Copper**Conductor Dia. (mm):** 0.50 ± 0.01 **Insulation:** Skin-FPE-Skin**Insulation Dia. (mm):** $0.9 \pm 0.03 \times 2C$

Twist x 5P x 4

Binder: on each 5 pair**Jelly Filled****Tape :** Mylar Sprial**Jacket:** PE**Outer Dia. (mm):** 11.6 ± 0.25 **Colour:****The colour of the insulation(Each 5 pair):** White, Blue ;White , Orange ; White , Green ; White ,
Brown ; White ,Grey ; Red, Blue ; Red , Orange ; Red ,
Green ; Red , Brown ;

Red , Grey

The jacket colour: Black**Marking(3times/m):**

RS 5202807 CW 1128 TELECOM 20PR

Performance:**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<96

Min.Insulation DC Resistance at 20°C ($G\Omega$ *KM) :
>1.5

Mutual capacitance (at 800Hz) (nF/KM) : <64

Pair-to pair capacitance unbalance (at 800Hz)(pF/500M) : 275

