






PRODUCT
P/N: XXXXX-XXXX



500 SETS PER POLY BAG
P/N: 89707-0001



4000 SETS PER CARTON BOX
P/N: 89499-9027

FUNCTIONAL SYMBOLS F A = 0 F C = 0

F

P

DIVISIONAL SYMBOLS

molex

PACKAGING SPECIFICATION (BAG 89707-0001)

PRODUCT SALES DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
895420164	PSD	000	A

MATERIALS AND FINISHES


BODY: ZINC ALLOY
PLATED (SEE TABLE)
THICKNESS (SEE TABLE)

CENTER CONTACT: BRASS
PLATED GOLD (THICKNESS SEE TABLE)







INSULATOR: TEFLON

OUTER CONTACT (OC): BERYLLIUM COPPER
PLATED GOLD (THICKNESS SEE TABLE)

CRIMP TUBE: BRASS
PLATED (SEE TABLE)
THICKNESS (SEE TABLE)



RG179 CABLE



73415-4492	BAG	70 μ" MIN NICKEL	30 μ" MIN	30 μ" MIN	70 μ" MIN NICKEL
73415-4491	ONE PER BAG	GOLD FLASH	10 μ" MIN	5 μ" MIN	10 μ" MIN GOLD
73415-4490	BAG	GOLD FLASH	10 μ" MIN	5 μ" MIN	10 μ" MIN GOLD
PART NO.	PACKAGING	BODY FINISH	CONTACT FINISH	OC FINISH	CRIMP TUBE FIN

CHG: BAG WAS BULK PER RF17-E062 EC NO: URF2017-0344 DRWN: LIN CHKD: CHENG APPR: YCHENG A5	DESCRIPTION 2017/03/27 2017/03/29	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY TEF	DATE 2003/08/11	TITLE MCX PLUG STR FOR RG179		
			4 PLACES	± .005	± .0004	CHECKED BY SSS	DATE 2003/08/11	75 OHMS	
			3 PLACES	± .003	± .0002	APPROVED BY GMH	DATE 2003/08/11	MCX-PC EWR-2114	
			2 PLACES	± .002	± .0001	MATERIAL NO. DOCUMENT NO.		MOLEX MOLEX INCORPORATED	
			ANGULAR ± 2 °		SEE TABLE		SD-73415-449		SHEET NO. 1 OF 1
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				