



NTS „eSwift“ Series

NTS ES WIFT A-1232 EHB

Order no	RS 138461
Scope of delivery	
Accessory set	EHB electric power tool dust extractor
Mains Voltage	240 V
Filter bag	RS 8112230
Features	
Main filter	RS 7753912
Pulse filter cleaning	no
Appliance socket	yes
Speed controller	no
Blowing function	no
Carry handle with cable hook	yes
Hose fixing	no
Hose winding and connector fixture	yes
Park position	yes
Gentle start	yes
After-running	yes
Water level detection	yes
Antistatic prepared	no
Push handle	no
Pipe clip	no
Accessory storage	yes
Technical specifications	
Power consumption (max.)	Watt 1200
Volume flow (max.)	l/s 70
Vacuum (max.)	mbar 210
Container volume (max.) Gross-Dust-Water	l 32/27/20
Sound pressure level Schalldruckpegel	db(A) 72.5
Dimensions L/W/H	cm 39,5 x 39 x 56,3
Weight	kg 7.5
Power cable length	m 5,0 HIGH VISABILITY PVC, red
Reach	m 8,2 - 9,2

Powerful Dust extraction unit Power-tool take off auto start 110v socket and plug wet pick up as well as dry