

70402

Crevice Scrub, 225 mm, Very hard, Green



The crevice scrub is suitable for cleaning difficult to reach areas under and between equipment since the handle can be positioned parallel to the floor. The filaments are placed in an arrow shape that ensures very efficient cleaning of even small cracks and crevices. The middle row of filaments are stiffer than the other filaments to form a very stiff scrubbing brush.

Technical Data

Item Number	70402
Visible bristle length	40 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Patent Pending No.	US D786,565 S
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	1100 Pcs
Quantity Per Layer (Pallet)	1 Pcs.
Box Length	320 mm
Box Width	230 mm
Box Height	160 mm
Length	225 mm
Width	35 mm
Height	90 mm
Gross Weight	0,24 kg
Net Weight	0,22 kg
Cubik metre	0,0012 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Mark 7	No
Gtin-13 Number	5705022001350
GTIN-14 Number (Box quantity)	15705028001368
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact