

**0605 - FLUOROPOLYMER TAPE**



**working temperature** -250 to 260 °C  
-418 to 500 °F  
23 to 533 °K

**body** FKM

[Convert to oz](#) [Reset Filters](#)

**Part Nb**

 (kg)

0605 12 12

.012

---