

# PROSAFE LED SWIVEL HEADED LANTERN

PS-L3/L3RK



**SEOUL** **BEAMMASTER**  
LENS

**10**  
HOURS  
RUNTIME

**250**  
METRE  
BEAM RANGE

**300**  
LUMENS  
OUTPUT

**IPX4**  
WATER  
RESISTANCE

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Optical Beammaster lens for beam penetration
- » Swivel head rotation 135°
- » Easy screw battery replacement
- » Side charging point
- » Impact resistant to 1M

<b>BATTERY</b>	1 x 6v PJ996 Lantern battery (Not Included)
<b>WEIGHT</b>	420g (with battery)
<b>DIMENSION</b>	250 x 110mm



WALL BRACKET (INC)



CARRY STRAP (INC)

## PS-L3RK

Rechargeable Kit including PS-L3 LED Lantern, PS-RB2 Rechargeable Battery, UK252 Mains Charger, UK253 12/24v Vehicle Charger, Carry Strap and Wall Mounting Bracket.

