

Main

Range	Resi9
Product or component type	Door kit
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 flush-mounting rack

Complementary

Enclosure mounting	Flush
Type of front cover	Plain
Door opening side	Reversible
Number of horizontal rows	6
9 mm pitches	26
Number of 18 mm modules per row	2 x 13
Total number of 18 mm modules	130
Provided equipment	1 door
Standards	NF C 15-100
IP degree of protection	IP40
IK degree of protection	IK09 conforming to EN 50102
Net weight	11.45 kg
Quantity per set	1
Width	590 mm
Height	1070 mm
Depth	22 mm
Colour tint	White (RAL 9003)
Targeted country	France

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes