

Datasheet

RS Pro Eyebolt M12

RS Stock No: **673-642**



Product Details

RS Pro eyebolt with M12 thread size, is suitable for use in a wide range of lifting applications. This eyebolt is proof tested and supplied completely with test certificate. It is a high quality metric eyebolt with collar to BS4278. This eyebolt made of carbon steel, has a diameter of 15 mm.

Features and Benefits

- M12 thread size
- 15mm thread length
- Made of carbon steel
- 0.4t working load limit



ENGLISH

Specifications:

| | |
|----------------------|--------------|
| Diameter | 15 mm |
| Material | Carbon Steel |
| Thread Length | 18 mm |
| Thread Size | M12 |
| Working Load Limit | 0.4 t |
| Collar Diameter | 22 mm |
| Collar Thickness | 7 mm |
| Eye Outside Diameter | 33 mm |
| Overall Height | 54 mm |
| Standards Met | BS 4278:1984 |