



### Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Fixing frame
Range compatibility	Mureva Styl
Colour tint	White (RAL 9003)
Sale per indivisible quantity	1

### Complementary

Device mounting	Flush
Number of gangs	1 gang
Condition of use	Indoor/Outdoor
Material	PC
Length	84 mm
Height	28 mm
Width	84 mm
Projecting depth	19 mm

### Environment

Quality labels	AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing $\geq 650$ °C according to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C