

Data Sheet

Polyurethane Re-coil Hose

With male swivel (PT) fitting and spring on both end

RS Stock No. 700-5655

RS Stock No. 700-5664

RS Stock No. 700-5667

PRODUCT DESCRIPTION

- LIGHT / FLEXIBLE / EASY USE / LESS FATIGUING
- Polyurethane is on tough plastic, use in everything from skate board.
- Exceptional wear and kink resistant
- Recoil that lasts and lasts. The COIL has a memory that you can depend on.
- Fitting replacement made easy and reusable



SPECIFICATION

Materials: UCS 98A Polyurethane Ester base, Shore A98 ± 2

Temperature Range: -20°C ~ 70°C

Working Length: 80% ~ 90% of material length

Article No	Hose ID*OD (mm)	Hose Length (M)	Coil ID (mm)	Working Length (M)	Color	W.P (bar)	Thread size
700-5655	5*8	2.5	35	2	blue	12	1/4"
700-5664	5*8	5	35	4	blue	12	1/4"
700-5667	5*8	7.5	35	6	blue	12	1/4"
700-5661	6.5*10	2.5	50	2	blue	9	1/4"
700-5670	6.5*10	5	50	4	blue	9	1/4"
700-5673	6.5*10	7.5	50	6	blue	9	1/4"
700-5677	8*12	2.5	60	2	blue	10	3/8"
700-5686	8*12	5	60	4	blue	10	3/8"
700-5689	8*12	7.5	60	6	blue	10	3/8"
700-5683	5*8	2.5	60	2	red	12	1/4"
700-5692	5*8	5	60	4	red	12	1/4"
700-5695	5*8	7.5	60	6	red	12	1/4"
700-5699	6.5*10	2.5	60	2	red	9	1/4"
700-5709	6.5*10	5	60	4	red	9	1/4"
700-5702	6.5*10	7.5	60	6	red	9	1/4"
700-5706	8*12	2.5	60	2	red	10	3/8"
700-5715	8*12	5	60	4	red	10	3/8"
700-5718	8*12	7.5	60	6	red	10	3/8"

Note:

Hose tail 500 mm /10 mm
 With male swivel fitting (PT) and spring on both end.
 1 pc Bag

