

# LED cord dimmer T26.07

Item-no.: 2600x0700(i) (transparent) | 2620x0700(i) (black) | 2660x0700(i) (white)



Suitable for dimmable LED lamps, incandescent, HV- and LV-halogen lamps with magnetic transformer Operates quietly

Opportunity for optimized and flicker-free dimming of LED-lamps

No stand-by consumption because of real on / off switch

Overload/short-circuit protection

Integrated protective conductor terminal

Applicable as intermediate and end device due to different connection opportunities

EHMANN advantage - 100 % quality check, 5 years warranty, German manufacturer

EHMANN service - LED recommendation

EHMANN quality – High-grade manufacturing and reliable function













## LED cord dimmer T26.07

#### Technical data

3 - 35 W **LED** rated power 7 - 110 W/VA **Rated power** 

230 V ~ (+/-10%) / 50 Hz Rated voltage

Suitable for dimmable LED lamps, incandescent, HV- and LV-halogen lamps with magnetic transformer

Operating principle: leading edge

Function: On /off via separate switch; dimming via slide switch (for

hand- and foot use)

Temperature protection: thermal fuse

Overload/short circuit protection: fuse 5x20mm T1AH/250 V

Max. cord diameter: 6,5 mm Cut-off: Complete cut-off Cycle of operation: >50.000

Connection: Screw terminal 0,5 - 1,5 mm<sup>2</sup> (flexible)

Mode of operation: S1 Protection class: 2 Safety class: IP20 Contamination level: 1



















### Opportunity for optimized and flicker-free dimming of LED lamps

In emergence of flickering-effects during dimming an LED lamp, there is the possibility of adjusting the minimum brightness, in order to optimize the dimming behaviour.




#### **LED lamp recommendation**

Shows which LEDs are compatible with this dimmer.

Available via QR code or online at www.ehmann-gmbh.de



Connection diagram as intermediate or end device



Item-no. 2600x0700(i) (transparent) EAN 401209600446 2

Item-no. 2620x0700(i) (black) Item-no. 2660x0700(i) (white)

EAN 4012096003847 EAN 401209600385 4 PU 10 PU 10 PU 10

130 x 59 x 35 mm Dimensions (L x W x H)