



Lighting **excellence**



@4liteuk



@4liteuk



@4lite



@4liteuk

Pylus

Pylus Oval Wall Light White

Code: 4L2/3217

Application Commercial

Product Features

- Polycarbonate oval bulkhead
- Fast loop-in / loop-out connections
- Body options of black or white
- PIR option available
- Suitable for external semi-commercial and residential applications
- CCT selectable between 3000K, 4000K and 6500K
- Polycarbonate opal diffuser
- Non-dimmable

Technical Information

Wattage	12W
Lumens Delivered	1100lm (4000K)
Lm/W	88lm/W (4000K)
Beam Angle	110
CRI	80
CCT	3000/4000/6000K
Input	220-240V
Operating Temp	-5°C - 25°C
SDCM	6
Product Weight without Packaging	0.289 kg

Technical Information

Light Source	LED
Colour / Finish	White
IP Rating	IP54
Class Protection	2
Internal / External	External
Mounting Option	Ceiling, Wall
Lumen Depreciation	L80 54,000h
Warranty (Years)	4
CE Mark	Yes
Diameter	0 mm
Height	0 mm