



ENGLISH

RS Pro Datasheet

Green, smooth, flexible, lightweight pressure hose with anti-static, charge-eliminating inner rubber layer. For use in car paint shops, paint cabins, paint guns, etc. Resistant to chemicals and solvents. Ideal for nitro lacquer. The hose must be flushed with solvent before use. Silicone-free surface ensures problem-free painting. For maximum safety, please consult the chemical resistance list. Normally installed using brass fittings, and either hose clamps or crimped-on low-pressure fittings. Please contact Codan for further information.

Application: Paint Spray

Standard Length: 25 metres

Working Temperature: -40°C to 100°C

Inside: EPDM

Colour: Black

Reinforcement: PVA

Outside: EPDM

Colour: Green

Standards: -

Inside dia. (mm)	Outside dia. (mm)	Working Pressure BAR	Burst Pressure BAR	Bend Radius (mm)	Weight (g/m)
6,0	12,4	20	60	40	127
9,0	16,0	20	60	50	188
11,0	18,0	20	60	55	218
13,0	21,0	20	60	60	247
16,0	24,0	20	60	75	342