

FR28 - Bizflame Work FR Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre, 280g

Outer Carton: 12



Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Work fabric.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

EN 17353 Type B2

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Two tier knee pad pockets allowing two positioning options
- Side access openings
- Sleeve pocket
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

FR28 - Bizflame Work FR Coverall
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13017-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR28GNRXS	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406715	15036108891921
FR28GNRS	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406692	15036108891907
FR28GNRM	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406685	15036108891891
FR28GNRL	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406678	15036108891884
FR28GNRXL	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406708	15036108891914
FR28GNRXXL	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406722	15036108891938
FR28GNRXXXL	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406739	15036108891945
FR28GNR4XL	Green	43.0	28.0	46.0	1.3100	0.0554	5036108406661	15036108891877