

STYLE #	CONSTRUCTION	GAUGE	LINER MATERIAL	COATING MATERIAL	CUFF STYLE	COLOUR	EN SIZE	LENGTH MM	PACKAGING
76-200	Knitted	13	Nylon	N/A	Knitwrist	White	7, 8, 9, 10	190 - 235	12 pairs in a bag, 12 bags in a carton
76-202	Knitted	13	Nylon	N/A	Knitwrist	White	6, 7, 8, 9, 10, 11	195 - 245	12 pairs in a bag, 12 bags in a carton
76-160	Knitted	13	Polyester Cotton	N/A	Knitwrist	Natural	7, 8, 9, 10	230 - 260	12 pairs in a bag, 12 bags in a carton
76-100	Knitted	10	Cotton	N/A	Knitwrist	Natural	7, 9	215	12 pairs in a bag, 12 bags in a carton
76-261	Knitted	7	Polyester Nylon Cotton	N/A	Knitwrist	Natural	7, 9	230	12 pairs in a bag, 12 bags in a carton



Light, stretchy gloves available in various materials and finishes

PRIMARY INDUSTRIES



IDEAL APPLICATIONS

- General handling
- Delicate manipulation
- Fine assembly of dry parts
- Application of mastic, sealers in paintshops
- Packaging

DESCRIPTION

- Can be worn on their own or as liners. Good value product protection.
- No seams to rub or irritate. Permits a longer, more comfortable wear, with no weak points which might split or fray.
- Stringknit construction allows good air flow to the hand. Hands don't become hot and sweaty.
- Ambidextrous. No need to pair, therefore more economical.
- All styles washable at 40°C. Will not shrink, stiffen or lose their shape. More hygienic for the wearer. Better value for the provider.
- 76-200 & 76-202: nylon versions, softer, more comfortable, flexible and low lint.

REMARKS

- 76-100, 76-200 & 76-202: Fit for special purpose
- 76-202 = Category I

76-200:214X
76-160:114X
76-100:002X
76-261:113X



CATEGORY II

Print date: 07-05-2014

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu