

# **FEATURES**

- Various threads are available
- Completely sealed against dust
- Excellent water resistance
- Made with high quality Nylon 66
- Locknut supplied

# RS PRO M32 Cable Gland with Locknut, Nylon, IP68

RS Stock No.: 822-9754



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



# **Product Description**

Brought to you by RS PRO, a range of metric threaded cable glands offering excellent strain relief and cable protection. Cable glands allow you to mount a cable into a pre-drilled hole. Commonly used within construction and by electrical engineers, cable glands are simple and easy to use. Each gland is rated as IP68, ensuring the level of cable protection is incredibly resilient to the outdoors and other harsh environments. All models are highly reliable and excellent quality.

#### **General Specifications**

Thread Size	M32
Material	Nylon 66
Colour	Grey
Pack size	10
Locknut Included	yes
Application	Machinery with delicate internals, Telecommunications, Flow meters, Underwater power generators

# **Mechanical Specifications**

Maximum Cable Diameter	25mm
Minimum Cable Diameter	18mm
Thread Length L2	34.5mm
Seals B1	25mm
Protrusion Length L1	14.7mm
Nut L3	25.7mm
Thread inner diameter D2	26mm
Thread outer diameter D1	32mm

# **Protection Category**


IP Rating	IP68



# Approvals

Compliance/Certifications	EN 61340
Standards Met	UL 94 V-2





RS PART NUMBER	DESCRIPTION	D1	D2	B1	L1	L2	L3	Cable Range	COLOR	Packsize
8229739	round topCable GlandM12 x 1.5 Grey IP68	12	8.3	6.9	7.9	19.6	13.6	3~6.5		
8229748	round topCable GlandM16 x 1.5 Grey IP68	16	10.9	10.5	15.5	23.4	16.9	5~10	GREY	
8229741	round topCable GlandM20 x 1.5 Grey IP68	20	15	14	15	28.5	18.5	10~14		
8229757	round topCable GlandM20S x 1.5 GreylP68	20	15	14	10	28.5	18.5	10~14		
8229745	round topCable GlandM25 x 1.5 Grey IP68	25	18.6	18.4	15.2	29.4	22.3	13~18		
8229751	round topCable GlandM25S x 1.5 Grey IP68	25	18.6	18.4	10	29.4	22.3	13~18		10
8229754	round topCable GlandM32 x 1.5 Grey IP68	32	26	25	14.7	34.5	25.7	18~25		
8229767	round topCable GlandM16 x 1.5 White IP68	16	10.9	10.5	15.5	23.4	16.9	5~10		
8229776	round topCable GlandM20 x 1.5 White IP68	20	15	14	15	28.5	18.5	10~14		
8229782	round topCable GlandM20S x 1.5 WhiteIP68	20	15	14	10	28.5	18.5	10~14	WHITE	
8229779	round topCable GlandM25 x 1.5 White IP68	25	18.6	18.4	15.2	29.4	22.3	13~18	VVHILE	
8229785	round topCable GlandM25S x 1.5 WhitelP68	25	18.6	18.4	10	29.4	22.3	13~18	1	
8229773	round topCable GlandM32 x 1.5 White IP68	32	26	25	14.7	34.5	25.7	18~25		
8229760	round topCable GlandM20S x 1.5 BlackIP68	20	15	14	10	28.5	18.5	10~14	DI ACIZ	
8229763	round topCable GlandM25S x 1.5 BlackIP68	25	18.6	18.4	10	29.4	22.3	13~18	BLACK	
8229789	round topCable GlandM20 x 1.5 Red IP68	20	15	14	15	28.5	18.5	10~14	DED	
8229798	round topCable GlandM25 x 1.5 Red IP68	25	18.6	18.4	15.2	29.4	22.3	13~18	RED	